

# InnoPette™ Pipette Mini Max™ Centrifuge

**beyonlab**®

# Innovation Comfortable and Accuracy

**BeyonLab® InnoPette™ series**

## Ensuring Precise

无级调节，精准吸液

## Ergonomic Handle

人体工程学设计，结实耐用

## One-Handed Volume Adjustment

单手操作，调节方便



## Volume Lock

锁扣设计，量程稳定

## Comfortable Finger Hook

舒适挂钩，降低疲劳


## Features

- ◆ The plunger glides smoothly at every setting, ensuring precise aspiration every time.
- ◆ Comfortable, Ergonomic Handle; Small, Lightweight, Rugged Body: The InnoPette pipettes are lightweight with a small handle and conveniently-placed finger hook. Made of high-density, chemical-resistant polymer, they won't crack or break even if dropped.
- ◆ Comfortable Finger Hook: The conveniently-placed finger hook allows the user to rest his hand and grip the pipette more lightly during use. The pipettes can be held in a variety of positions to further reduce repetitive strain (RSI).
- ◆ One-Handed Volume Adjustment: Simply turning the plunger allows the user to adjust volume using only one hand. The snag-proof design allows rapid adjustment even with gloves on. Easy-to-read dials show volume in microliters, greatly reducing the chance of error.
- ◆ Volume Lock: A slight turn of the volume setting lock prevents accidental volume changes.

## 产品特点

- ◆ 无级调节，确保每次精准吸液。
- ◆ 人体工程学设计，由耐腐蚀材料制成，舒适轻便，结实耐用。
- ◆ 舒适挂钩设计，降低手部疲劳，有效避免重复性肌肉劳损。
- ◆ 单手操作，调节方便，三位数字显示避免读数错误。
- ◆ 锁扣设计，保证量程稳定。





| Model No. | Cat. No. | Volume (uL ) | Increment (uL ) | R el. % | Abs uL | R el. CV% | Abs S D uL |
|-----------|----------|--------------|-----------------|---------|--------|-----------|------------|
| INO2      | 110001   | 0.2          | 0.002           | 12.0    | 0.024  | 6.00      | 0.012      |
|           |          | 1            |                 | 2.7     | 0.027  | 1.30      | 0.013      |
|           |          | 2            |                 | 1.5     | 0.030  | 0.70      | 0.014      |
| INO10     | 110002   | 1            | 0.02            | 2.5     | 0.025  | 1.20      | 0.012      |
|           |          | 5            |                 | 1.5     | 0.075  | 0.60      | 0.030      |
|           |          | 10           |                 | 1.0     | 0.10   | 0.40      | 0.040      |
| INO20     | 110003   | 2            | 0.02            | 7.5     | 0.15   | 2.00      | 0.040      |
|           |          | 5            |                 | 3.0     | 0.15   | 0.90      | 0.045      |
|           |          | 10           |                 | 1.5     | 0.15   | 0.50      | 0.050      |
|           |          | 20           |                 | 1.0     | 0.20   | 0.30      | 0.060      |
| INO100    | 110004   | 10           | 0.2             | 3.5     | 0.35   | 1.00      | 0.10       |
|           |          | 50           |                 | 0.8     | 0.40   | 0.24      | 0.12       |
|           |          | 100          |                 | 0.8     | 0.80   | 0.15      | 0.15       |
| INO200    | 110005   | 20           | 0.2             | 2.5     | 0.5    | 1.00      | 0.20       |
|           |          | 100          |                 | 0.8     | 0.8    | 0.25      | 0.25       |
|           |          | 200          |                 | 0.8     | 1.6    | 0.15      | 0.30       |
| INO1000   | 110006   | 100          | 2.0             | 3.0     | 3.0    | 0.60      | 0.6        |
|           |          | 500          |                 | 0.8     | 4.0    | 0.20      | 1.0        |
|           |          | 1000         |                 | 0.8     | 8.0    | 0.15      | 1.5        |
| INO5000   | 110007   | 500          | 5.0             | 2.4     | 12.0   | 0.60      | 3.0        |
|           |          | 1000         |                 | 1.2     | 12.0   | 0.30      | 3.0        |
|           |          | 2500         |                 | 0.6     | 15.0   | 0.20      | 5.0        |
|           |          | 5000         |                 | 0.6     | 18.0   | 0.16      | 8.0        |



# Mini in Size Max in Function

## BeyonLab® Mini Max™ series

The MiniMax is the perfect answer for quick spin-downs of tube walls and caps, HPLC preparations, micro-filtration tubes, PCR strips and short-term cold room use. Its tiny footprint makes it perfect for desktop use or for quick transferring between countertops. And many color options for different lab styles.

### Features

- ◆ **Safe** Centrifuge cannot be operated when cover is open.
- ◆ **Simple** Simply shut the lid to begin operation and open to stop.
- ◆ **Small** Tiny footprint can squeeze easily onto a crowded countertop.
- ◆ **Silent** Excellent motor and rubber foot grip ensure noise-free, sure-footed operation.
- ◆ **Speed** 6000RPM; 8000RPM; 10000RPM
- ◆ **OEM available, Custom rotor design**

### 产品特点

- ◆ 外观：流线型设计，体积小，美观大方。
- ◆ 材料和工艺：采用高品质的复合材料，和现代生产工艺，严格的质量保证体系。
- ◆ 安全设计：采用翻盖开关功能，开盖即自动停止；外盖采用复合材料，不易破碎。
- ◆ 电机：采用航空用微型直流无刷电机，保证了产品持久耐用。
- ◆ 电压：采用世界最先进的宽频电源技术，输入电压85V~245V多适用，保证运行品质。
- ◆ 功能：随机配置两个转头和两种套管，一机多用。
- ◆ 噪音低。




| Model Name. | Cat No. | Speed(RPM) | Capacity(ml)            | Notes             |
|-------------|---------|------------|-------------------------|-------------------|
| Minimax     | 3000001 | 6800       |                         |                   |
| Rotor1      | No.1    | 6800       | 6*1.5/2.0(6*0.5, 6*0.2) | fixed-angle rotor |
| Rotor2      | No.2    | 6800       | 2x8-well 0.2ml          | strip rotor       |



# Universal Adapters For Many Centrifuge Brands

## 提供各大品牌离心机转子适配器



1, 25ml universal tube    2, 15ml conical tube  
3, 50ml DIN round bottom tube    4, 50ml round bottom tube  
...







**BeyonLab Scientific Instrument** *Pipette / Centrifuge / Spectrophotometer*

**Tel** +86 21 3371 2213

**Email** sales@beyonlab.com

**Fax** +86 21 3371 2213

beyonlab@hotmail.com

For more informations please visit: **[www.beyonlab.com](http://www.beyonlab.com)**

®™ Trademark of The BeyonLab Scientific Instrument Co.,Ltd.

Beyonlab is improving its quality. Styles and specifications may be changed in the future. Please visit [www.beyonlab.com](http://www.beyonlab.com) for the latest informations.